

Design bathroom scale KERN MGD



HOME CARE





Elegant look combined with large, flat glass weighing plate to make it easier to step on and give maximum safety

Features

- · Elegant design
- · Sturdy glass weighing plate
- MGD-L: particularly large weighing plate for secure, comfortable standing position
- · For easy and hygienic cleaning
- Particularly flat design facilitates access
- Generous weighing range
- Secure and non-slip positioning with rubber feet
- · Easy to operate: simply tap on it – stand on it – read the weight
- Integrated AUTO-OFF function to preserve the batteries
- Weight displayed in kg or lb
- II Large high-contrast display that is easy to read
- 2 Delivered in appealing packaging
- · Note: The models are only delivered in a set of 5 units. I.e. the price given in the table refers to a delivery of 5 items. Cannot be delivered individually.

Technical data

MGD 100K-1

- · LCD display, digit height 40 mm
- · Batteries included, 2×CR2032, operating time up to 100 h

MGD 200K1L

- LCD display, digit height 50 mm
- · Batterien inklusive, 3×1,5 V AAA, operating time up to 100 h

Accessories

· Cleaning cloths, alcohol-free cloths for wipe disinfectant, quick-acting, on basis of modern quaternary ammonium compounds, and also against papova viruses. Particularly gentle on materials, and therefore very well suited for the disinfection of alcohol sensitive medical products. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 80 pcs., size 20×22 cm per cloth KERN MYC-01

STANDARD









Model	Weighing range	Readability	Weighing plate	Net weight	
KERN	[Max] kg	[d] kg	mm	kg	
MGD 100K-1S05	180	0,1	300×300×19	1,5	
MGD 200K-1LS05	250	0,1	380×330×27	2	



Pictograms



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required.



Data interface RS-232:

To connect the balance to a printer, PC or network.



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals.



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software:

to transfer the measurements from the device to a PC.



GLP/ISO-Protokoll:

With date and time. Only with KERN printers.



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight.



Totalising level A:

The weights of similar items can be added together and the total can be printed out.



Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. Please refer to website for more details.



Weighing with tolerance range:

(Check weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



Hold function:

When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight.



Hold function:

When the weighing conditions are unstable, a stable weight is calculated as an average



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram.



Stainless steel:

The balance is protected against corrosion.



Suspended weighing:

Load support with hook on the underside of the balance.



Battery operation:

Ready for battery operation. The battery type is specified for each device.



Rechargeable battery pack:

Rechargeable set.



Battery operation rechargable:

Prepared for a rechargable battery operation



Universal mains adapter:

with universal input and optional input socket adapters for A) EU, CH B) EU. CH. GB. USA



Mains adapter:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available.



Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body.



PEAK

Peak hold function:

capturing a peak value within a measuring process.



Push and Pull:

the measuring device can capture tension and compression forces.



Integrated scale:

In the eyepiece.



360° rotatable microscope head



Monocular Microscope:

For the inspection with one eye.



Binocular Microscope:

For the inspection with both eyes



Trinocular Microscope:

For the inspection with both eyes and the additional option for the connection of a



Abbe Condenser:

With high numerical aperture for the concentration and the focusing of light.



Halogen illumination:

For pictures bright and rich in contrast.



LED illumination:

Cold, energy saving and especially long-life illumination.



Fluorescence illumination for compound microscopes:

With 100W mercury lamp and filter.



Fluorescence illumination for compound microscopes:

With 3W LED illumination and filter.



Phase contrast unit:

For a higher contrast.



Darkfield condenser/unit:

For a higher contrast due to indirect illumination



Polarising unit:

To polarise the light.



Infinity system:

Infinity corrected optical system.



ATC

Automatic temperature compesation: For measurements between 10 °C and 30 °C



Verification possible:

The time required for verification is specified in the pictogram.



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram.

^{*}The Bluetooth® word mark and logos are registered trademarks owned Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.